

Rittal – The System.

Faster – better – everywhere.



TP 6702.600

Pedestals

State: 2026-02-10 (Source: rittal.com/ca-en)



FRIEDHELM LOH GROUP



TP 6702.600 - Pedestals

TopConsole pedestals, four widths and two different depths provide the basis for every TopConsole solution. The AX lock plate ensures a uniform appearance, and two-part gland plates are included with the supply for simple cable routing.

Features

| | |
|--------------------------------------|--|
| Model No. | TP 6702.600 |
| Material | Housing: Carbon steel, 1.5 mm Door and console lid: Carbon steel, 2.0 mm, all-round foamed-in PU seal Mounting plate: Carbon steel |
| Surface finish | Housing, cover and door: Dipcoat-primed, powder-coated on the outside, textured paint Mounting panel: Zinc-plated |
| Color | RAL 7035 |
| Supply includes | Housing open at top Door or double door with locking rod (with depth 400 mm at the front, with depth 500 mm at the front and rear) Mounting panel Base Plates |
| Dimensions of mounting plate (W x H) | 1,099 mm x 625 mm |
| Number of doors | 2 |
| Dimensions | Width: 1,200 mm Height: 675 mm Depth: 400 mm |
| Protection category IP to IEC 60529 | IP 55 |
| Protection category NEMA | NEMA 12 |
| Note | The sliding element VX 5051.172 can be used as a mounting aid for the VX base/plinth system, new design |
| Packaging unit | 1 pc(s). |

Features

| | |
|-----------------------|---------------|
| Net weight | 58 |
| Gross weight | 60.5 |
| Customs tariff number | 94032080 |
| EAN | 4028177959866 |
| ETIM 9 | EC000784 |
| ETIM 8 | EC000784 |
| ECLASS 8.0 | 27180504 |

Approvals

| | |
|--------------|---|
| Approvals | UL + C-UL (listed) |
| Explanations | Declaration of conformity Declaration of conformity UK |