

# Rittal – The System.

Faster – better – everywhere.



## TP 6703.600 Pedestals

State: 2025-08-29 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TP 6703.600 - Pedestals

TopConsole pedestals, four widths and two different depths provide the basis for every TopConsole solution. The AX lock plate ensures a uniform appearance, and two-part gland plates are included with the supply for simple cable routing.

## Features

|                                      |  |
|--------------------------------------|--|
| Model No.                            | TP 6703.600  |
| Material                             | Housing: Carbon steel, 1.5 mm<br>Door and console lid: Carbon steel, 2.0 mm, all-round foamed-in PU seal<br>Mounting plate: Carbon steel                               |
| Surface finish                       | Housing, cover and door: Dipcoat-primed, powder-coated on the outside, textured paint<br>Mounting panel: Zinc-plated   |
| Color                                | RAL 7035   |
| Supply includes                      | Housing open at top<br>Door or double door with locking rod (with depth 400 mm at the front, with depth 500 mm at the front and rear)<br>Mounting panel<br>Base Plates |
| Dimensions of mounting plate (W x H) | 1,499 mm x 625 mm  |
| Number of doors                      | 2  |
| Dimensions                           | Width: 1,600 mm<br>Height: 675 mm<br>Depth: 400 mm   |
| Protection category IP to IEC 60529  | IP 55  |
| Protection category NEMA             | NEMA 12  |
| Note                                 | The sliding element VX 5051.172 can be used as a mounting aid for the VX base/plinth system, new design  |
| Packaging unit                       | 1 pc(s).   |

# Features

|                       |               |
|-----------------------|---------------|
| Net weight            | 75            |
| Gross weight          | 80            |
| Customs tariff number | 94032080      |
| EAN                   | 4028177959873 |
| ETIM 9                | EC000784      |
| ETIM 8                | EC000784      |
| ECLASS 8.0            | 27180504      |

# Approvals

|              |   |
|--------------|---|
| Approvals    | UL + C-UL (listed)  |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |