



CX 6713.000 - CX Desk Unit

Four widths form the bridge for a two- or three-part construction of the CX desk system.



Features

| | |
|-----------------|---|
| Model No. | CX 6713.000 |
| Version | Center section |
| Material | Housing: Carbon steel, 1.5 mm Console cover: Carbon steel 2.0 mm, all-round foamed-in PU seal |
| Surface finish | Housing and cover: Dipcoat primed, powder-coated on the outside, textured paint |
| Color | RAL 7035 |
| Supply includes | Housing Cover hinged at rear, 2 stays with automatic locking. Unlatching automatically on the left, manually on the right Opening for cable entry into the enclosure base Lock: 3 mm double-bit Housing Cover hinged at bottom, including cover retainer Open base for individual cable entry |
| Dimensions | Width: 1,600 mm Depth: 745 mm |
| Height, front | 130 mm |
| Height rear | 200 mm |

Features

| | |
|-------------------------------------|---|
| IK code | IK10 |
| Note | To close the desk unit, a closure plate is required For a 2-piece console setup, a pedestal and a closure plate for the desk unit are required For a 3-piece console setup, a pedestal and console top-section are required |
| Protection category IP to IEC 60529 | IP 55 |
| Protection category NEMA | NEMA 1 NEMA 12 |
| Base material | Carbon steel |
| Dimensions | Width: 1,600 mm |
| No. of locks | 3 |
| Lock version | Cam |
| Lock Insert | 3 mm double-bit |
| Lock | Lock version: Cam No. of locks: 3 Lock Insert: 3 mm double-bit |
| Packaging unit | 1 pc(s). |
| Net weight | 46 kg |
| Gross weight | 47 kg |
| Customs tariff number | 94032080 |
| ETIM 9 | EC000784 |
| ETIM 8 | EC000784 |
| ECLASS 8.0 | 27180504 |
| Product description | CX console system, desk unit, width: 1600 mm |

Approvals

Approvals

| | |
|--------------|---------------------------|
| Approvals | UL + C-UL (listed) |
| Explanations | Declaration of conformity |
