Rittal – The System.

Faster – better – everywhere.





CX 6720.000 **CX Console Top-Section**

State: 2025-11-16 (Source: rittal.com/ca-en)



CX 6720.000 - CX Console Top-Section

Four widths offer the best conditions for individual monitoring and a three-part construction of the CX desk system.





Features

Model No.	CX 6720.000
Version	Top piece
Product description	Four widths offer the best conditions for individual monitoring and a three-part construction of the CX desk system.
Material	Housing: Carbon steel, 1.5 mm Door: Carbon steel, 2.0 mm, all-round foamed-in PU seal
Surface finish	Housing and door: Dipcoat primed, powder-coated on the outside, textured paint
Color	RAL 7035
Supply includes	Housing Cover hinged at bottom, including cover retainer Open base for individual cable entry Lock: 3 mm double-bit
Dimensions	Width: 600 mm Height: 515 mm
Top depth	125 mm
Bottom depth	245 mm
IK code	IK10
Note	For a 3-piece console setup, a desk unit and pedestal are required

© Rittal 2025

Features

Protection category IP to IEC 60 529	IP 55
Protection category NEMA	NEMA 1
	NEMA 12
Base material	Carbon steel
Dimensions	Width: 600 mm
	Height: 515 mm
	Top depth: 125 mm
	Bottom depth: 245 mm
No. of locks	2
Lock version	Cam
Lock Insert	3 mm double-bit
Lock	Lock version: Cam
	No. of locks: 2
	Lock Insert: 3 mm double-bit
Packaging unit	1 pc(s).
Net weight	15
Gross weight	16.8
Customs tariff number	94032080
EAN	4028177983687
ETIM 9	EC000784
ETIM 8	EC000784
ECLASS 8.0	27180504

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity

© Rittal 2025 3