## Rittal – The System.

Faster – better – everywhere.





# CX 6740.000 CX One-Piece Console

State: 2025-11-16 (Source: rittal.com/ca-en)



## CX 6740.000 - CX One-Piece Console

One-piece console for operating and monitoring, with large mounting plate and a high protection category of IP 55, available in four different widths.







#### **Features**

Model No.	CX 6740.000
Version	One-piece consoles
Material	Housing: Carbon steel, 1.5 mm  Door and console lid: Carbon steel, 2.0 mm, all-round foamed-in PU seal  Mounting plate: Carbon steel, 2.5 mm
Surface finish	Housing, cover and door: Dipcoat-primed, powder-coated on the outside, textured paint  Mounting panel: Zinc-plated
Color	RAL 7035
Supply includes	Housing, solid back and sides  Door or double door at front, with 3-point locking system  Mounting panel  Cover with cam locks, hinged at rear, 2 stays with automatic locking.  Unlocking automatically on the left, manually on the right.  Gland plate  Lock: 3 mm double-bit
Dimensions	Width: 1,000 mm Height: 970 mm Depth: 400 mm

© Rittal 2025 2

## Features

Dimensions of mounting plate (W x H)	920 mm x 900 mm
Top depth	495 mm
Bottom depth	400 mm
Number of doors	2
IK code	IK10
Protection category IP to IEC 60 529	IP 55
Protection category NEMA	NEMA 1 NEMA 12
Base material	Carbon steel
Dimensions	Width: 1,000 mm Height: 970 mm Top depth: 495 mm Bottom depth: 400 mm
Packaging unit	1 pc(s).
Net weight	72
Gross weight	75.25
Customs tariff number	94032080
EAN	4028177983632
ETIM 9	EC000784
ETIM 8	EC000784
ECLASS 8.0	27180504

# Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity

© Rittal 2025 3