


Rittal – The System.

Faster – better – everywhere.



DK 7000.630

Socket strip in plastic housing

State: 2025-08-19 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7000.630 - Socket strip in plastic housing

230 V outlet strips, unrestricted use, including angular connectors, thanks to the arrangement of the plug-in contacts in a long row.



Features

Model No.	DK 7000.630
Product description	8-way socket strip for Schuko connector type (type F, CEE 7/4). The strip can be mounted on the enclosure frame vertically or in the rear 482.6 mm (19") profile. Space greater than 2 U is required in the 482.6 mm (19") profile. The outlets are arranged at a 45° angle, making it easy to insert right-angle plugs. The connection cable is fitted in a terminal slot in the strip. The terminal slot has a separate cover and has external terminals to provide separate grounding.
Material	Plastic
Supply includes	Connection cable Fastening Screws 2 serrated washers Captive nuts M6, conductive Nuts
Version	Without switch
Outlets	8 x D, ground pin (type F, CEE 7/3)
Length of connection cable	2 m
Connection cable (type)	H05VV-F3G1.5 with wire end ferrules
Rated operating voltage	230 V AC, 50 Hz

Features

Rated voltage	230 V AC, 50 Hz
Rated current (max.)	16 A
Type of connection (electrical)	Wire end ferrules
Installation options	TE 7000, rear 482.6 mm (19") section (> 2 U) TE 7000, vertically mounted on the frame
Socket color	Black
Packaging unit	1 pc(s).
Net weight	0.92
Gross weight	1.026
Customs tariff number	85366990
EAN	4028177438569
ETIM 9	EC000330
ECLASS 8.0	27142604

Approvals

Explanations	Declaration of conformity
--------------	---------------------------