

Rittal – The System.

Faster – better – everywhere.



IT 7100.510 OCP doors set

State: 2025-07-15 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



IT 7100.510 - OCP doors set for R-OCP ORV3 rack

For increased access protection including comfort handle with push-button and lock insert.



Features

Model No.	IT 7100.510
Benefits	Greater access protection Optimal service access through asymmetrically divided rear door
Material	Carbon steel
Surface finish	dipcoat-primed and powder-coated
Color	RAL 9005
Supply includes	Front door, one-piece, vented Asymmetrically divided rear door, vented Front and rear comfort handles with push button keyed door lock 12 hinges
Dimensions	Width: 596 mm Height: 2,236 mm Depth: 35 mm
Packaging unit	2 pc(s).
Customs tariff number	94039910
EAN	4028177998612
ETIM 9	EC000747