

Rittal – The System.

Faster – better – everywhere.



DK 7111.224

Cable routing bars, 19" attachment

State: 2025-12-14 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7111.224 - Cable routing bars, 19" attachment

For structured routing of entire cable bundles, 19" attachment, connection comb.



Features

| | |
|-------------------------|--|
| Model No. | DK 7111.224 |
| Product description | For structured routing of bundled cables. The cable routing bars may be secured in a variety of different positions inside the enclosure. |
| Applications | For horizontal cable routing within the distributor level. Our unique open mounting hole design allows installation of the cable routing bars through the 19" mounting rails with the mounting screws of the installed components. |
| Material | Support: Carbon steel Cable routing bars, connection combs: Plastic UL 94-V0 |
| Color | RAL 9005 |
| Supply includes | Cable Routing Bars Connection combs |
| Number connection combs | 2 |
| Note | Size of individual chambers (HxD) approx. 34 x 100 mm |
| Height units | 4 U |
| Packaging unit | 4 pc(s). |
| Net weight | 0.6 |

Features

| | |
|-------------------------------------|--|
| Gross weight | 0.727 |
| PCF/VE (cradle-to-gate) | 2.8 kg CO2 eq (Cat B) |
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |
| Customs tariff number | 73269098 |
| EAN | 4028177550377 |
| E-Number Sweden | E7282519 |
| ETIM 9 | EC000322 |
| ECLASS 8.0 | 27400604 |