

Rittal – The System.

Faster – better – everywhere.



DK 7151.305

Blanking panel, 19" (482.6 mm)

State: 2026-02-08 (Source: [ittal.com/ca-en](https://www.ittal.com/ca-en))



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

DK 7151.305 - Blanking panel, 19" (482.6 mm) Tool-free attachment

Used to blank unused areas within the 482.6 mm (19") mounting level.

Features

Model No.	DK 7151.305
Product description	The blanking panel is used to cover unused areas within the 482.6 mm (19") mounting level. Tool-free quick-release fastening allows for easy installation in any location, and removal if necessary. The consistent use of blanking panels ensures targeted ventilation in partially occupied racks.
Technical specifications	Height units 3 U (3 x 1 U)
Material	Plastic Fire behavior according to UL 94 HB, halogen-free
Surface finish	Matt
Color	RAL 9005
Supply includes	Blanking panel, 3 U, with integral quick-fastening
Build-up height	3 U
Dimensions	Width: 482.6 mm
Packaging unit	3 pc(s).
Net weight	1.011
Gross weight	1.16
Customs tariff number	39269097
EAN	4028177709263
E-Number Sweden	E7239529
ETIM 9	EC000456
ECCLASS 8.0	27189217