
Rittal - The System.

Faster - better - everywhere.






State: 2025-11-17 (Source: rittal.com/ca-en)



DK 7400.000 - Data Rack

Data Rack for optimum accessibility from all sides during assembly and installation, and a high degree of mobility when twin castors are used.







Features

Model No.	DK 7400.000
Material	Profile frame, base/plinth: Carbon steel Feet: Die-cast zinc
General color	RAL 7035
Color	Profile frame, base/plinth: RAL 7035 Panel, feet: RAL 5018
Supply includes	Torsionally rigid profile frame with 482.6 mm (19") holes Stable base/plinth with integral feet, with the option of floor anchoring without base trim panels Mounting Accessories
Dimensions	Width: 550 mm Height: 1,900 mm Depth: 750 mm
Height units	40 U
Distance from the second mounting level, 50 mm hole pattern	150 - 350 mm
Hole pattern between the mounting levels	50 mm

© Rittal 2025

Features

Load capacity of the 19" levels	1,500 N
Note	Order second mounting level separately
Base material	Carbon steel
Packaging unit	1 pc(s).
Net weight	18.5
Gross weight	19.5
PCF/VE (cradle-to-gate)	75.4 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	94032080
EAN	4028177129979
E-Number Sweden	E7239648
ETIM 9	EC002507
ECLASS 8.0	27180602

© Rittal 2025 3