## Rittal - The System.

Faster – better – everywhere.





# DK 7480.035 Energy-Box, 482.6 mm (19")

State: 2025-12-15 (Source: rittal.com/ca-en)



## DK 7480.035 - Energy-Box, 482.6 mm (19")

Depth-variable top hat rail for installed equipment to DIN 43 880, sizes 1-3, to accommodate a maximum of 22 items.

### **Features**

Model No.	DK 7480.035	
Product description	Depth-variable top hat rail for installed equipment to DIN 43 880 sizes 1 – 3, e.g. to accommodate flush-type outlets, circuit breakers, etc. with rear cable clamping and one N and one PE rail each on insulated base.	
Color	RAL 7035	
Supply includes	Energy-box with depth-variable top hat rail for installed equipment to DIN 43880, sizes 1-3, with brush strip for cable entry at rear Plastic hood including reserve panel cover (UL 94-V0) 44 connection clamps, 4 mm² 2 connection clamps, 16 mm² 2 blanking covers 12 clips for strain relief of the connection cables Labeling strips, self-adhesive	
Max. pitch units @ 18 mm	22	
Note	Individual population with circuit-breakers at the factory available on request.	
Dimensions	Width: 482.6 mm Height: 132.5 mm Depth: 155 mm	
Height units	3 U	
Packaging unit	1 pc(s).	
Net weight	2.354	
Gross weight	2.54	
Customs tariff number	85366990	
EAN	4028177166004	

© Rittal 2025

### **Features**

E-Number Sweden	E7239593	
ETIM 9	EC002620	
ECLASS 8.0	27189261	

© Rittal 2025 3