

Rittal – The System.

Faster – better – everywhere.



DK 7480.035

Energy-Box, 482.6 mm (19")

State: 2026-06-22 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7480.035 - Energy-Box, 482.6 mm (19")

Depth-variable top hat rail for installed equipment to DIN 43 880, sizes 1 – 3, to accommodate a maximum of 22 items.

Features

Model No.	DK 7480.035
Product description	Depth-variable top hat rail for installed equipment to DIN 43 880 sizes 1 – 3, e.g. to accommodate flush-type outlets, circuit breakers, etc. with rear cable clamping and one N and one PE rail each on insulated base.
Color	RAL 7035
Supply includes	Energy-box with depth-variable top hat rail for installed equipment to DIN 43880, sizes 1-3, with brush strip for cable entry at rear Plastic hood including reserve panel cover (UL 94-V0) 44 connection clamps, 4 mm ² 2 connection clamps, 16 mm ² 2 blanking covers 12 clips for strain relief of the connection cables Labeling strips, self-adhesive
Max. pitch units @ 18 mm	22
Note	Individual population with circuit-breakers at the factory available on request.
Dimensions	Width: 482.6 mm Height: 132.5 mm Depth: 155 mm
Height units	3 U
Packaging unit	1 pc(s).
Net weight	2.354 kg
Gross weight	2.54 kg
Customs tariff number	85366990
ETIM 9	EC002620

Features

ECLASS 8.0

27189261

Product description

DK Energy-Box, WHD: 482,6 (19")x132,5x155 mm, max. 22 pitch units