

Rittal – The System.

Faster – better – everywhere.



CP 7495.000

Twin castors

State: 2026-01-15 (Source: [ittal.com/ca-en](https://www.ittal.com/ca-en))



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

CP 7495.000 - Twin castors

For mobile use, can be mounted directly on the enclosure.

Features

Model No.	CP 7495.000
Product description	For mobile use, can be mounted directly on the enclosure.
Color	Black
Supply includes	4 twin castors, 2 x with, 2 x without locks. Assembly components
Note on Model No.:	When mounting on a VX base/plinth, the base/plinth adapter is required When mounting on a TS base/plinth, the base/plinth adapter is required
Suitable for	Enclosure type: VX Enclosure type: VX IT Enclosure type: VX SE Enclosure type: PC Enclosure type: TP pedestals Enclosure type: IW Enclosure type: Data Rack Enclosure type: Chiller
Clearance floor	125 mm
Max. load capacity (static) per component	1,200 N
Dimensions	Thread: M12 x 20
Packaging unit	4 pc(s).
Net weight	1.76
Gross weight	1.98
Customs tariff number	83024900
EAN	4028177131200
E-Number Sweden	E7239729

Features

ETIM 9 EC002621

ECLASS 8.0 27189262