
## Rittal – The System.

Faster – better – everywhere.





## DK 7541.000 Ground rail, vertical

State: 2025-10-28 (Source: rittal.com/ca-en)



## DK 7541.000 - Ground rail, vertical for VX, VX IT

The supplied ground conductors facilitate star grounding of cable clamp straps on patch panels, ground terminals are fully adjustable, rail current carrying capacity approx. 200 A.

## **Features**

| Model No.                    | DK 7541.000   |
|------------------------------|---|
| Product description          | Easy to mount on 25 mm DIN hole pattern on distributor or on 482.6 mm (19") punched rails. The supplied ground conductors facilitate star grounding of cable clamp straps on patch panels. The ground terminals are fully adjustable. Rail current carrying capacity approx. 200 A. |
| Supply includes              | Ground rail made from E-Cu 57 to DIN EN 12 163, DIN EN 13 601, 15 x 5 mm null 15 grounding leads 6 mm², L = 500 mm Assembly components  |
| Dimensions                   | Length: 545 mm  |
| Suitable for                 | Enclosure type: VX<br>VX IT<br>TS<br>Height: 800 mm   |
| Packaging unit               | 1 pc(s).  |
| Net weight                   | 1.272   |
| Gross weight                 | 1.472   |
| Copper weight (kg per piece) | 0.35  |
| Customs tariff number        | 74198090  |
| EAN                          | 4028177131798   |
| ETIM 9                       | EC000329  |
| ECLASS 8.0                   | 27400605  |

© Rittal 2025 2