

# Rittal – The System.

Faster – better – everywhere.



## DK 7548.000

## Ground rail, vertical

State: 2025-12-08 (Source: [rittal.com/ca-en](https://rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7548.000 - Ground rail, vertical for VX, VX IT

The supplied ground conductors facilitate star grounding of cable clamp straps on patch panels, ground terminals are fully adjustable, rail current carrying capacity approx. 200 A.

## Features

Model No.	DK 7548.000
Product description	Easy to mount on 25 mm DIN hole pattern on distributor or on 482.6 mm (19") punched rails. The supplied ground conductors facilitate star grounding of cable clamp straps on patch panels. The ground terminals are fully adjustable. Rail current carrying capacity approx. 200 A.
Supply includes	Ground rail made from E-Cu 57 to DIN EN 12 163, DIN EN 13 601, 15 x 5 mm null 15 grounding leads 6 mm <sup>2</sup> , L = 500 mm Assembly components
Dimensions	Length: 1,945 mm
Suitable for	Enclosure type: VX VX IT TS Height: 2,200 mm
Packaging unit	1 pc(s).
Net weight	2.407
Gross weight	2.74
Customs tariff number	74198090
EAN	4028177131934
ETIM 9	EC000329
ECLASS 8.0	27400605