

**Rittal – The System.**

Faster – better – everywhere.



**DK 7608.510**

**Socket strip in plastic housing**

State: 2025-12-16 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7608.510 - Socket strip in plastic housing

230 V outlet strips, unrestricted use, including angular connectors, thanks to the arrangement of the plug-in contacts in a long row.



## Features

Model No.	DK 7608.510
Product description	8-way socket strip for Schuko connector type (type F, CEE 7/4). The strip can be mounted on the enclosure frame vertically or in the rear 482.6 mm (19") profile. Space greater than 2 U is required in the 482.6 mm (19") profile. The outlets are arranged at a 45° angle, making it easy to insert right-angle plugs. The connection cable is fitted in a terminal slot in the strip. The terminal slot has a separate cover and has external terminals to provide separate grounding.
Material	Plastic
Supply includes	Connection cable Fastening Screws 2 serrated washers Captive nuts M6, conductive Nuts
Version	Without switch
Outlets	12 x CH (type J, SEV 1011)
Dimensions	Length: 793 mm
Length of connection cable	2 m
Connection cable (type)	H05VV-F3G1.5 with wire end ferrules

# Features

Rated operating voltage	230 V AC, 50 Hz
Rated voltage	230 V AC, 50 Hz
Rated current (max.)	10 A
Installation options	Components with a 25 mm pitch pattern Enclosure frame
Packaging unit	1 pc(s).
Net weight	1.6
Gross weight	1.8
Customs tariff number	85366990
EAN	4028177162709
ETIM 9	EC000330
ECLASS 8.0	27142604