

# Rittal – The System.

Faster – better – everywhere.



DK 7641.000

## AE Wall-Mounted Housings

State: 2026-02-01 (Source: [ittal.com/ca-en](https://www.ittal.com/ca-en))



FRIEDHELM LOH GROUP

# DK 7641.000 - AE Wall-Mounted Housings with 19" (482.6 mm) profile rails, depth-variable

Wall-mounted housing for small networks with fixed 19" mounting level and flange plate with brush strip for cable entry at the bottom. Protection category IP 55.

## Features

|                                    |   |
|------------------------------------|---|
| Model No.                          | DK 7641.000   |
| Product description                | Wall-mounted housing for small networks with a high protection category.  |
| Material                           | Housing: Carbon steel   |
| Surface finish                     | Housing: Powder-coated<br>Profile rails: Zinc-plated  |
| Color                              | RAL 7035  |
| Supply includes                    | Housing with hinged door<br>Door hinged on the right, may be swapped to the left<br>Cam lock with 3 mm double-bit insert<br>Flange plate with brush strip for cable entry in the enclosure base<br>Profile rails, 482.6 mm (19"), fully depth adjustable<br>C rail, for cable clamping on the rear panel<br>Metal bracket for optional accommodation of a ground rail or a 19" socket strip |
| Height units                       | 8 U   |
| Dimensions                         | Width: 600 mm<br>Height: 380 mm<br>Depth: 350 mm  |
| Installation depth                 | 310 mm  |
| Installation height for components | 8 U   |
| Position door catch                | right, may be swapped to the left   |
| No. of locks                       | 1   |
| Base material                      | Carbon steel  |

# Features

---

|                                     |  |
|-------------------------------------|--|
| Protection category IP to EN 60 529 | Up to IP 66 (depending on the selected flange plate) |
| Gland plate                         | Size: 5<br>Qty.: 1                                   |
| Packaging unit                      | 1 pc(s).   |
| Net weight                          | 17.23  |
| Gross weight                        | 18.137   |
| Customs tariff number               | 94032080   |
| EAN                                 | 4028177147027  |
| E-Number Sweden                     | E7239953   |
| ECLASS 8.0                          | 27180208   |

# Approvals

---

|           |            |
|-----------|------------|
| Approvals | TÜV<br>VDE |
|-----------|------------|