

# Rittal – The System.

Faster – better – everywhere.



## DK 7645.000

# AE Wall-Mounted Housings

State: 2026-06-21 (Source: [rittal.com/ca-en](http://rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7645.000 - AE Wall-Mounted Housings with 19" (482.6 mm) profile rails, depth-variable

Wall-mounted housing for small networks with fixed 19" mounting level and flange plate with brush strip for cable entry at the bottom. Protection category IP 55.

## Features

Model No.	DK 7645.000
Product description	Wall-mounted housing for small networks with a high protection category.
Material	Housing: Carbon steel
Surface finish	Housing: Powder-coated Profile rails: Zinc-plated
Color	RAL 7035
Supply includes	Housing with hinged door Door hinged on the right, may be swapped to the left Cam lock with 3 mm double-bit insert Flange plate with brush strip for cable entry in the enclosure base Profile rails, 482.6 mm (19"), fully depth adjustable C rail, for cable clamping on the rear panel Metal bracket for optional accommodation of a ground rail or a 19" socket strip
Height units	16 U
Dimensions	Width: 600 mm Height: 760 mm Depth: 350 mm
Installation depth	310 mm
Installation height for components	16 U
Position door catch	right, may be swapped to the left
No. of locks	2
Base material	Carbon steel

# Features

---

Protection category IP to EN 60529	Up to IP 66 (depending on the selected flange plate)
Gland plate	Size: 5 Qty.: 1
Packaging unit	1 pc(s).
Net weight	29.7 kg
Gross weight	30.1 kg
Customs tariff number	94032080
ETIM 9	EC002500
ECLASS 8.0	27180208
Product description	DK Wall-mounted enclosures AE, WHD:600x760x350 mm, 16 U, AE 1376

# Approvals

---

Approvals	TÜV VDE
-----------	------------