

# Rittal – The System.

Faster – better – everywhere.



## DK 7688.000 19" profile rails

State: 2026-05-22 (Source: [rittal.com/ca-en](http://rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7688.000 - 19" profile rails for DK PS, CS New Basic housings

For installing 19" components in network and server racks and in CS New Basic outdoor housings

## Features

Model No.	DK 7688.000
Product description	For installing 19" components in DK PS network and server racks and in CS New Basic outdoor housings. The profile rails are depth-adjustable in the 25 mm hole pattern. An installation bracket is required to mount the profile rails.
Material	Carbon steel
Surface finish	Zinc-plated
Supply includes	Mounting accessories
Height units	24 U
Installation dimensions	Installation depth for components: 482.6 mm Installation width for components: 19"
Suitable for	Enclosure type: CS basic housings DK PS Height: = 1,200 mm
Packaging unit	2 pc(s).
Net weight	2.494 kg
Gross weight	2.693 kg
PCF/VE (cradle-to-gate)	10.3 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	73269098
ETIM 9	EC002620
ECLASS 8.0	27189261

# Features

---

Product description

DK 482.6 mm (19") mounting angles, 24 U, For H: 1200 mm