

Rittal – The System.

Faster – better – everywhere.



DK 7688.000 19" profile rails

State: 2026-07-07 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7688.000 - 19" profile rails for DK PS, CS New Basic housings

For installing 19" components in network and server racks and in CS New Basic outdoor housings

Features

Model No.	DK 7688.000
Product description	For installing 19" components in DK PS network and server racks and in CS New Basic outdoor housings. The profile rails are depth-adjustable in the 25 mm hole pattern. An installation bracket is required to mount the profile rails.
Material	Carbon steel
Surface finish	Zinc-plated
Supply includes	Mounting accessories
Height units	24 U
Installation dimensions	Installation depth for components: 482.6 mm Installation width for components: 19"
Suitable for	Enclosure type: CS basic housings DK PS Height: = 1,200 mm
Packaging unit	2 pc(s).
Net weight	2.494 kg
Gross weight	2.693 kg
PCF/VE (cradle-to-gate)	10.3 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	73269098
ETIM 9	EC002620
ECLASS 8.0	27189261

Features

Product description

DK 482.6 mm (19") mounting angles, 24 U, For H: 1200 mm