

# Rittal – The System.

Faster – better – everywhere.



## DK 7709.135

## Wall-mounted enclosures EL, 3-part

State: 2025-07-31 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7709.135 - Wall-mounted enclosures EL, 3-part with punched rails and profile rails, depth-variable

Wall-mounted housing 3-part, pre-configured with: Solid flange plate, top and bottom, punched rails, C rails, wall mounting bracket. Protection category IP 55.

## Features

|                     |  |
|---------------------|--|
| Model No.           | DK 7709.135  |
| Version             | Wall-mounted housing IT<br>with punched rails and profile rails, depth-variable  |
| Product description | Wall-mounted enclosure with hinged door provides optimum accessibility.  |
| Material            | Wall and hinged part: Carbon steel, 1.5 mm<br>Viewing window: Single-pane safety glass, 3 mm   |
| Surface finish      | Powder-coated  |
| General color       | RAL 7035   |
| Color               | Wall and hinged part: RAL 7035<br>Viewing door: RAL 7035/7015 (slate gray)   |
| Supply includes     | Wall section closed at top and bottom with flange (gland) plate, two vertical mounting rails and horizontal C-profile rails for cable clamping.<br>Hinged part with 25 mm pitch pattern in the front and rear frame, two 482.6 mm (19") profile angles at the front, fully depth adjustable<br>4 wall mounting brackets 10 mm<br>Designer viewing door<br>1 enclosure key double bit no. 5<br>Mini-comfort handle for lock inserts<br>Security lock 3524 E |
| Height units        | 9 U  |
| Dimensions          | Width: 600 mm<br>Height: 478 mm<br>Depth: 473 mm   |
| Installation depth  | 420 mm   |

## Features

|                                       |   |
|---------------------------------------|---|
| Clearances                            | Clearance width: 502 mm<br>Clearance height: 415 mm |
| Depth hinged part                     | 316 mm  |
| Depth of wall section                 | 135 mm  |
| IK code                               | IK08  |
| Load capacity of hinged part (static) | 450 N   |
| Base material                         | Carbon steel  |
| Protection category IP to EN 60 529   | IP 55   |
| Packaging unit                        | 1 pc(s).  |
| Net weight                            | 29.45   |
| Gross weight                          | 31  |
| Customs tariff number                 | 94032080  |
| EAN                                   | 4028177324183                                       |
| ETIM 9                                | EC000261  |
| ECLASS 8.0                            | 27142408  |

## Approvals

|           |                    |
|-----------|--------------------|
| Approvals | UL + C-UL (listed) |
|-----------|--------------------|