Rittal - The System.

Faster – better – everywhere.





DK 7709.735 Wall-mounted enclosures EL, 3-part

State: 2025-11-28 (Source: rittal.com/ca-en)



DK 7709.735 - Wall-mounted enclosures EL, 3-part preconfigured with profile rails, depth-variable

Wall-mounted housing 3-part, pre-configured with: Solid flange plate, top, with brush strip at the bottom, mounting rails, C rails, outlet filter, ground rail, wall-mounting bracket

Features

Model No.	DK 7709.735	
Version	Wall-mounted housing IT	
	pre-configured with profile rails, depth-variable	
Product description	Wall-mounted enclosure with hinged door provides optimum	
	accessibility.	
Material	Wall and hinged part: Carbon steel, 1.5 mm	
	Viewing window: Single-pane safety glass, 3 mm	
Surface finish	Powder-coated	
General color	RAL 7035	
Color	Wall and hinged part: RAL 7035	
	Viewing door: RAL 7035/7015 (slate gray)	
Supply includes	Wall section with solid gland plate at the top and brush strip at the	
	bottom, two vertical mounting rails and C rail, horizontal, for cable clamping	
	Hinged part with 25 mm pitch pattern in the front and rear frame,	
	two 482.6 mm (19") profile angles at the front, fully depth adjustable	
	and side outlet filters on left and right	
	Ground rail with star grounding	
	Designer viewing door	
	1 enclosure key double bit no. 5	
	Wall mounting brackets, 10 mm	
	Mini-comfort handle for lock inserts	
	Security lock 3524 E	
Height units	9 U	

© Rittal 2025

2

Features

Dimensions	Width: 600 mm Height: 478 mm Depth: 573 mm	
Installation depth	520 mm	
Clearances	Clearance width: 502 mm Clearance height: 415 mm	
Depth hinged part	416 mm	
Depth of wall section	135 mm	
IK code	IK08	
Load capacity of hinged part (static)	450 N	
Base material	Carbon steel	
Protection category IP to EN 60 529	IP 54 in conjunction with solid gland plate top and bottom	
Packaging unit	1 pc(s).	
Net weight	33.25	
Gross weight	35	
Customs tariff number	94032080	
EAN	4028177324237	
E-Number Sweden	E7239957	
ETIM 9	EC000261	
ECLASS 8.0	27142408	

Approvals

7. pp. 0. 4.0	Approvals	UL + C-UL (listed)	
---------------	-----------	--------------------	--

© Rittal 2025 3