Rittal - The System.

Faster – better – everywhere.





DK 7712.135 Wall-mounted enclosures EL, 3-part

State: 2025-11-29 (Source: rittal.com/ca-en)



DK 7712.135 - Wall-mounted enclosures EL, 3-part with punched rails and profile rails, depth-variable

Wall-mounted housing 3-part, pre-configured with: Solid flange plate, top and bottom, punched rails, C rails, wall mounting bracket. Protection category IP 55.

Features

Model No.	DK 7712.135
Version	Wall-mounted housing IT
	with punched rails and profile rails, depth-variable
Product description	Wall-mounted enclosure with hinged door provides optimum accessibility.
Material	Wall and hinged part: Carbon steel, 1.5 mm Viewing window: Single-pane safety glass, 3 mm
Surface finish	Powder-coated
General color	RAL 7035
Color	Wall and hinged part: RAL 7035
	Viewing door: RAL 7035/7015 (slate gray)
Supply includes	Wall section closed at top and bottom with flange (gland) plate, two vertical mounting rails and horizontal C-profile rails for cable clamping. Hinged part with 25 mm pitch pattern in the front and rear frame,
	two 482.6 mm (19") profile angles at the front, fully depth adjustable
	4 wall mounting brackets 10 mm
	Designer viewing door
	1 enclosure key double bit no. 5 Mini-comfort handle for lock inserts
	Security lock 3524 E
Height units	12 U
Dimensions	Width: 600 mm
	Height: 612 mm
	Depth: 473 mm
Installation depth	420 mm

© Rittal 2025

Features

Clearances	Clearance width: 502 mm Clearance height: 549 mm
Depth hinged part	316 mm
Depth of wall section	135 mm
IK code	IK08
Load capacity of hinged part (static)	600 N
Base material	Carbon steel
Protection category IP to EN 60 529	IP 55
Packaging unit	1 pc(s).
Net weight	34.2
Gross weight	36
Customs tariff number	94032080
EAN	4028177324190
ETIM 9	EC000261
ECLASS 8.0	27142408

Approvals

		_
Approvals	UL + C-UL (listed)	

© Rittal 2025 3