

Rittal – The System.

Faster – better – everywhere.



DK 7826.780

Roof Plate, Vented

State: 2025-07-21 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7826.780 - Roof Plate, Vented for TS, TS IT

To replace the standard roof, with and without cable entry.



Features

Model No.	DK 7826.780
Version	One-piece without cable entry
Product description	To replace standard roof. 72 mm high roof plate, all-round vent slots, clamping profile for cable entry. The two-piece design with cable entry allows for easy retro-fitting.
Material	Carbon steel
Color	RAL 7035
Suitable for	Enclosure type: TS TS IT Width: 800 mm Depth: 1,000 mm
Packaging unit	1 pc(s).
Net weight	12.564
Gross weight	13.225
Customs tariff number	73269098
EAN	4028177345652
ETIM 9	EC000744
ECLASS 8.0	27182405