Rittal – The System.

Faster – better – everywhere.





DK 7827.100

Profile rails, 482.6 mm (19")

State: 2025-11-13 (Source: rittal.com/ca-en)



DK 7827.100 - Profile rails, 482.6 mm (19") for TS, CS Toptec

Profile rails in right-angled version. Profile rails are alternately available as L-shaped profile rails.

Features

Model No.	DK 7827.100	
Version	Cranked	
Benefits	Integral U markings in the front facilitate systematic assembly within the 19" level.	
Technical specifications	Integral 482.6 mm (19") punchings (EIA standard) Side round and square punchings Clear chromated for conductive connection of 19" fixtures	
Material	Carbon steel, 2 mm	
Supply includes	Assembly components	
Dimensions	Width: 482.6 mm	
Height units	20 U	
Note	The profile rails can also be used to accommodate 21", 23" and 24" attachment dimensions. Please select the slide rails according to the respective 19" plane spacing. For a combination with the L-shaped profile rails, the use of the mounting adapter for L-shaped profile rails is required.	
Suitable for	Enclosure type: TS 8 CS Toptec Height: 1,000 mm	
Packaging unit	2 pc(s).	
Net weight	2.844	
Gross weight	3.043	
Customs tariff number	73269098	
EAN	4028177234840	

© Rittal 2025

Features

ETIM 9	EC002620	
ECLASS 8.0	27189261	

© Rittal 2025 3