Rittal – The System.

Faster – better – everywhere.





DK 7827.180

Profile rails, 482.6 mm (19")

State: 2025-10-29 (Source: rittal.com/ca-en)



DK 7827.180 - Profile rails, 482.6 mm (19") for TS, CS Toptec

Profile rails in right-angled version. Profile rails are alternately available as L-shaped profile rails.

Features

Model No.	DK 7827.180
Version	Cranked
Benefits	Integral U markings in the front facilitate systematic assembly within the 19" level.
Technical specifications	Integral 482.6 mm (19") punchings (EIA standard)
	Side round and square punchings
	Clear chromated for conductive connection of 19" fixtures
Material	Carbon steel, 2 mm
Supply includes	Assembly components
Dimensions	Width: 482.6 mm
Height units	38 U
Note	The profile rails can also be used to accommodate 21", 23" and 24" attachment dimensions. Please select the slide rails according to the respective 19" plane spacing. For a combination with the L-shaped profile rails, the use of the mounting adapter for L-shaped profile rails is required.
Suitable for	Enclosure type: TS 8
	CS Toptec
	Height: 1,800 mm
Packaging unit	2 pc(s).
Net weight	5.266
Gross weight	5.543
Customs tariff number	73269098

© Rittal 2025

Features

E-Number Sweden	E7239756	
ETIM 9	EC002620	
ECLASS 8.0	27189261	

© Rittal 2025 3