

Rittal – The System.

Faster – better – everywhere.



DK 7827.200

Profile rails, 482.6 mm (19")

State: 2026-06-20 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7827.200 - Profile rails, 482.6 mm (19") for TS, CS Toptec

Profile rails in right-angled version. Profile rails are alternately available as L-shaped profile rails.

Features

| | |
|--------------------------|---|
| Model No. | DK 7827.200 |
| Version | Cranked |
| Benefits | Integral U markings in the front facilitate systematic assembly within the 19" level. |
| Technical specifications | Integral 482.6 mm (19") punchings (EIA standard) Side round and square punchings Clear chromated for conductive connection of 19" fixtures |
| Material | Carbon steel, 2 mm |
| Supply includes | Assembly components |
| Dimensions | Width: 482.6 mm |
| Height units | 42 U |
| Note | The profile rails can also be used to accommodate 21", 23" and 24" attachment dimensions. Please select the slide rails according to the respective 19" plane spacing. For a combination with the L-shaped profile rails, the use of the mounting adapter for L-shaped profile rails is required. |
| Suitable for | Enclosure type: TS 8 CS Toptec Height: 2,000 mm |
| Packaging unit | 2 pc(s). |
| Net weight | 5.842 kg |
| Gross weight | 6.26 kg |
| Customs tariff number | 73269098 |
| ETIM 9 | EC002620 |

Features

ECLASS 8.0

27189261