

Rittal – The System.

Faster – better – everywhere.



DK 7827.201

Profile rails, 482.6 mm (19")

State: 2026-01-30 (Source: rittal.com/ca-en)



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

DK 7827.201 - Profile rails, 482.6 mm (19") for TS

L profile rails, can also accommodate installation kits for server systems.

Features

Model No.	DK 7827.201
Version	L-shaped mounting angle
Benefits	<p>Integral U markings in the front facilitate systematic assembly within the 19" level.</p> <p>L rails accommodate the installation kits of server systems</p> <p>Suitable for 19" partial expansion</p>
Technical specifications	<p>Integral 482.6 mm (19") punchings (EIA standard)</p> <p>Side round and square punchings</p> <p>Clear chromated for conductive connection of 19" fixtures</p>
Material	Carbon steel, 2 mm
Supply includes	Assembly components
Height units	42 U
Note	<p>Please select the slide rails according to the respective 19" plane spacing.</p> <p>For a combination with the L-shaped profile rails, the use of the mounting adapter for L-shaped profile rails is required.</p>
Suitable for	<p>Enclosure type: TS</p> <p>Height: 2,000 mm</p>
Packaging unit	2 pc(s).
Net weight	4.642
Gross weight	4.842
Customs tariff number	73269098
EAN	4028177234949
E-Number Sweden	E3404324
ETIM 9	EC002620
ECLASS 8.0	27189261