

Rittal – The System.

Faster – better – everywhere.



DK 7831.726 Partition

State: 2025-07-31 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7831.726 - Partition for TS IT

Partition for TS IT. For rack mounting, suspended between two TS IT cabinets

Features

Model No.	DK 7831.726
Product description	Rack mounted, suspended between two enclosures. Each with three Ø 40 mm drilled holes in all 4 corners for the entry of wiring harnesses, ducting, etc. Drilled holes are sealed with the stepped collars supplied. To insert cable simply cut off the collar at the appropriate level for the cable diameter.
Material	Partition: Carbon steel Stepped collar: Plastic to UL 94-HB
Surface finish	Partition: Zinc-plated
Supply includes	Incl. 12 stepped collars dia. 40 mm
Suitable for	Enclosure type: TS IT Height: 2,200 mm Depth: 1,200 mm
Note	Use baying connector TS 8800.490. Not suitable for use in conjunction with a baying seal. Any seals that may be present must be removed prior to installation.
Packaging unit	1 pc(s).
Net weight	34
Gross weight	37
Customs tariff number	94039910
EAN	4028177517714
ETIM 9	EC002525
ECLASS 8.0	27189234