

# Rittal – The System.

Faster – better – everywhere.



## DK 7856.731

## Mounting frame, 482.6 mm (19")

State: 2026-06-23 (Source: rittal.com/usa-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7856.731 - Mounting frame, 482.6 mm (19") for TS, CS Basic and modular enclosures

To extend the front and rear 482.6 mm (19") level, the welded 482.6 mm (19") mounting frame can be fastened at variable depths.



## Features

Model No.	DK 7856.731
Product description	The welded 482.6 mm (19") mounting frame can be secured at variable depths and is used to lay out the front and rear 482.6 mm (19") level. The mounting frame has TS enclosure profile system punchings on the side and at the rear, to allow TS system accessories such as cable clamp rails, cable routing brackets, etc. to be mounted.
Material	Carbon steel
Surface finish	Zinc-plated
Supply includes	Assembly components
Dimensions	Width: 482.6 mm
Height units	42 U
Load capacity	Up to 10,000 N static load, with even load distribution on two 482.6 mm (19") mounting frames, with full installation.
Note	A combination of 482.6 mm (19") mounting frame plus fan mounting plate is not possible. For active ventilation, we recommend using with the modular fan roof.

# Features

---

Suitable for	Enclosure type: TS 8 CS basic housings CS Modular Enclosures Width: 800 mm Height: 2,000 mm
Packaging unit	1 pc(s).
Net weight	13 kg
Gross weight	14 kg
Customs tariff number	73269098
ETIM 9	EC002620
ECLASS 8.0	27189261