Rittal - The System.

Faster - better - everywhere.





SR 7858. Pivoting frame, large, panel

State: 2025-10-27 (Source:



SR 7858.100 - Pivoting frame, large, with trim panel for TS, VX SE, 800 mm wide enclosures

For 800 mm wide enclosures, 22 - 45 U, with trim panel to mount 482.6 mm (19") rack-mounted equipment.

Features

Model No.	SR 7858.100
Version	Heavy-duty version 19" level side
Product description	To mount 482.6 mm (19") equipment.
Material	Carbon steel
Surface finish	Frame: Zinc-plated Panel: Spray-finished
Color	RAL 7035
Supply includes	Locking rod system with double-bit lock insert Material for attaching Incl. installation kit for enclosure height 2000 mm
Opening angle	130°
Mounting tip	Depending on the installation situation TS punched sections with mounting flange, 23 x 73 mm, or TS punched sections with mounting flange, 17 x 73 mm are required
Note	See "Technical Details" for other expansion options In the case of TS and SE two-door enclosures with heights of 1800 mm or 2200 mm, the next smallest pivoting frame must be fitted to prevent a collision with the lock
Load capacity, static	350 kg
Suitable for	Enclosure type: TS VX SE Width: = 800 mm Height: = 2,000 mm
Height units	40 U

© Rittal 2025 2

Features

Suitable for enclosure type	TS VX SE
Packaging unit	1 pc(s).
Net weight	24.757
Gross weight	26.06
Customs tariff number	94039910
EAN	4028177438880
ETIM 9	EC002620
ECLASS 8.0	27189261

© Rittal 2025 3