

Rittal – The System.

Faster – better – everywhere.



DK 7858.200 Cable route, vertical

State: 2026-05-22 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7858.200 - Cable route, vertical for TS 8

For direct attachment between the roof and base frame of a 2000 mm high frame structure, installation position optionally on the inner or outer mounting level, route width 200 mm.



Features

Model No.	DK 7858.200
Product description	For direct attachment between the roof and base frame of a 2000 mm high enclosure. May be installed on the inner or outer mounting level. Route width 200 mm. With unique hole profile for securing various cable routing and management accessories.
Material	Carbon steel, zinc-plated
Supply includes	Assembly components
Dimensions	Width: 200 mm
Suitable for	Enclosure type: TS 8 Height: 2,000 mm
Packaging unit	1 pc(s).
Net weight	4.495 kg
Gross weight	4.66 kg
Customs tariff number	83024200
ETIM 9	EC000322
ECLASS 8.0	27400604