

Rittal – The System.

Faster – better – everywhere.



TE 7888.940 Distributor Racks

State: 2025-06-29 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TE 7888.940 - Distributor Racks TE 8000 open

For optimum accessibility from all sides during assembly and installation.

Features

Model No.	TE 7888.940
Benefits	Optimum accessibility from all sides during assembly and installation Unrestricted airflow, due to the open design The distance between mounting levels is infinitely variable
Material	Carbon steel
Surface finish	Powder-coated
General color	RAL 7035
Color	RAL 7035
Supply includes	Self-supporting mounting frame, with 482.6 mm (19") mounting level front and rear Roof-plate, prepared for accommodating a cable organizer Open base frame with 2 system chassis for individual configuration fitted in the width 4 leveling feet, M10 (supplied loose) Roof plate with horizontal brush strip at rear
Dimensions	Width: 600 mm Height: 2,000 mm Depth: 1,000 mm
Height units	42 U
Height units	42 U
Mounting space to 19" level, front/rear	80 mm / 130 mm
Distance between levels as delivered	745 mm
Load capacity	7,000 N
Base material	Carbon steel

Features

Packaging unit	1 pc(s).
Net weight	33
Gross weight	35
EAN	4028177801554
E-Number Sweden	E7282509
ETIM 9	EC002507
ECLASS 8.0	27180602