

Rittal – The System.

Faster – better – everywhere.



DK 7955.332

PDU international, switched version

State: 2026-05-23 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7955.332 - PDU international, switched version

Individually switchable output slots are the key performance feature of the PDU, which of course also offers a measuring function per phase/input. Current consumption data is shown on the OLED display.

Features

Model No.	DK 7955.332
Version	PDU, switched
Product description	Measurement function for each phase, as well as individually switchable output slots. Thanks to the compact PDU, all IT racks can easily be equipped with a professional power distribution system. In the case of the TS IT rack, mounting is even possible without tools. The compact design enables easy mounting. Due to the installation of bistable relays and an OLED display, the PDU has low energy consumption. An integrated web server enables direct network connection with comprehensive user management. The redundant power supply originates from all phases and also via an existing Power-over-Ethernet network. The PDU offers extensive management and monitoring functions. High reliability is guaranteed thanks to +/- 1% measurement accuracy.
Material	Aluminum section, black anodized
Supply includes	incl. H05-VV (3 m) connection cable with fitted input connector
Dimensions	Width: 44 mm Depth: 85 mm Length: 1,480 mm
Number of sockets and type	24 x C13 / 6 x C19
Outlets	24 x Non-Heating Apparatus Socket C13 6 x Non-Heating Apparatus Socket C19
Rated current (max.)	16 A
Infeeds	Qty.: 1 Phases per infeed: 3~
Length of connection cable	3 m

Features

Type of connection (electrical)	CEE
Guidelines	EMC Directive 2014/30/EU Low-Voltage Directive 2014/35/EU
Standards	EN 60950-1 IEC 61 000-4 IEC 61 000-6 EN 55 022
Operating temperature range	0 °C...45 °C
Ambient humidity (non-condensing)	10...95 %
Storage temperature range	-25 °C...70 °C
Suitable for	Enclosure type: TS IT: ≥ 1,800 mm
Packaging unit	1 pc(s).
Net weight	4.8 kg
Gross weight	6 kg
Customs tariff number	85366990
ECLASS 8.0	27142604
Product description	DK PDU international, switched version, Energy measurement per phase, switchable, WLD: 44x1480x85 mm, 24xC13, 6xC19, black, CEE, 3~, 16 A