

Rittal – The System.

Faster – better – everywhere.



SK 7980.000 Fan expansion kit

State: 2025-05-06 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 7980.000 - Fan expansion kit

For retro-fitting various fan units or to expand the fan mounting plate

Features

Model No.	SK 7980.000
Product description	Can be used as a stand-alone fan and for retrofitting various fan units or to extend the fan mounting plate.
Supply includes	Fans Connection cable (0.61 m) Assembly components
Unimpeded air flow (with fleece filter)	At 50 Hz: 160 m³/h At 60 Hz: 180 m³/h
Rated operating voltage	230 V, 1~, 50 Hz/60 Hz
Rated power P_{el}	At 50 Hz: 15 W At 60 Hz: 14 W
Dimensions	Width: 119 mm Height: 119 mm Depth: 38 mm
Operating temperature range	-10 °C...55 °C
Noise pressure level	At 50 Hz: 37 dB(A) At 60 Hz: 37 dB(A)
Packaging unit	1 pc(s).
Net weight	0.6
Gross weight	0.671
Customs tariff number	84149000
EAN	4028177137752
ETIM 9	EC000320
ECLASS 8.0	27180716