Rittal – The System.

Faster - better - everywhere.





SK 7990.000 Fan expansion kit

State: 2025-11-15 (Source: rittal.com/ca-en)



SK 7990.000 - Fan expansion kit for VX IT, TS IT

Fan expansion kit with integrated speed control for retrofitting in fan modules 5503.010, 5503.020 and 5503.025.

Features

Model No.	SK 7990.000
Version	Without roof plate
Product description	Fan expansion kit with integrated speed control for installation in fan modules 5503.xxx.
Benefits	Complete, ready-to-connect solution Energy-efficient speed control with preset characteristic curve International approvals and multi-voltage capability for worldwide use
Material	Plastic
Color	RAL 9005
Supply includes	Fans Protection grille Assembly components Installation and Short User's Guide
Air performance (at operating point)	150 m³/h
Rated operating voltage	24 V (DC)
Rated current max.	At 50 Hz: 0.32 A At 60 Hz: 0.32 A
Dimensions	Width: 119 mm Height: 25 mm Depth: 119 mm
Protection category IP to IEC 60 529	IP 20
Speed	100 %

© Rittal 2025

Features

Note	Reduction of the specified air flow to 150 m³/h at 25 Pa counter- pressure
Sound pressure level (at operating point)	44 dB(A)
Operating temperature range	5 °C55 °C
Rated power	7.7 W
Packaging unit	1 pc(s).
Net weight	0.3
Gross weight	0.308
Customs tariff number	84145915
EAN	4028177966345
ETIM 9	EC000320
ECLASS 8.0	27180716

© Rittal 2025 3