

# Rittal – The System.

Faster – better – everywhere.



## WM 8017.550

## WM wall-mounted enclosure

State: 2026-04-16 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# WM 8017.550 - WM wall-mounted enclosure double door

These double door wallmount enclosures can be used for virtually any application. The WM series ensures NEMA protection through a secure locking system, foamed-in-place gasket, and knife-edge sealing surface. Features include a cold rolled steel body and door, and a zinc plated mounting panel.

## Features

Model No.	WM 8017.550
Material	Door: Carbon steel, all-round foamed-in PU seal Housing: Carbon steel
Surface finish	Dipcoat-primed and powder-coated, textured paint Mounting panel: Zinc-plated
Color	RAL 7035
Supply includes	Housing with door(s) Mounting plate Rear wall mounting holes
Dimensions	Width: 1,050 mm Height: 600 mm Depth: 210 mm
Dimensions of mounting plate (W x H)	1,000 mm x 550 mm
Protection category NEMA	NEMA 12 NEMA 12
Material thickness - door	2 mm
Material thickness - enclosure	2 mm
Material thickness – mounting plate	2.5 mm
3-point locking system	Yes
Number of doors	2
Packaging unit	1 pc(s).

## Features

---

Net weight	99.206 lb
Gross weight	100.584 lb
Customs tariff number	8538100000

## Approvals

---

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity