

Rittal – The System.

Faster – better – everywhere.



WM 8017.595

WM wall-mounted enclosure

State: 2025-09-07 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



WM 8017.595 - WM wall-mounted enclosure single-door

These single door wallmount enclosures can be used for virtually any application. The WM series ensures NEMA protection through a secure locking system, foamed-in-place gasket, and knife-edge sealing surface. Features include a cold rolled steel body and door, and a zinc plated mounting panel.



Features

Model No.	WM 8017.595
Material	Door: Carbon steel, all-round foamed-in PU seal Housing: Carbon steel
Surface finish	Housing and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting panel: Zinc-plated
Color	RAL 7035
Supply includes	Housing with door(s) Door hinged on left Mounting plate Rear wall mounting holes 3-point latching L-Handle
Dimensions	Width: 900 mm Height: 1,200 mm Depth: 400 mm
Dimensions of mounting plate (W x H)	840 mm x 1,155 mm

Features

Protection category NEMA	NEMA 1 NEMA 3R NEMA 4 NEMA 12
Material thickness - door	2 mm
Material thickness - enclosure	2 mm
Material thickness – mounting plate	2.5 mm
3-point locking system	Yes
Packaging unit	1 pc(s).
Net weight	182.981
Gross weight	184.85
Customs tariff number	7326908688
UPC-Code	83172

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity