

Rittal – The System.

Faster – better – everywhere.



WM 8017.624

WM wall-mounted enclosure

State: 2026-04-03 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



WM 8017.624 - WM wall-mounted enclosure 316 stainless steel

These single door wallmount enclosures can be used for virtually any application. The WM series ensures NEMA protection through a secure locking system, foamed-in-place gasket, and knife-edge sealing surface. Features include a stainless steel 316L body and door, and a zinc plated mounting panel.



Features

| | |
|--------------------------------------|---|
| Model No. | WM 8017.624 |
| Material | Door: Stainless steel, all-round foamed-in PU seal Stainless steel 1.4404 (AISI 316L) Mounting plate: Carbon steel, zinc-plated |
| Surface finish | Brushed |
| Supply includes | Housing with door(s) Door hinged on left Mounting plate Wall mounting blind-nuts |
| Dimensions | Width: 500 mm Height: 500 mm Depth: 210 mm |
| Dimensions of mounting plate (W x H) | 449 mm x 470 mm |
| Protection category NEMA | NEMA 4X |
| Packaging unit | 1 pc(s). |
| Net weight | 35.999 lb |

Features

| | |
|-----------------------|------------|
| Gross weight | 35.999 lb |
| Customs tariff number | 8538100000 |

Approvals

| | |
|--------------|---------------------------|
| Approvals | UL + C-UL (listed) |
| Explanations | Declaration of conformity |
