

Rittal – The System.

Faster – better – everywhere.



WM 8018.521

WM wall-mounted enclosure

State: 2025-07-17 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



WM 8018.521 - WM wall-mounted enclosure 304 stainless steel

These single door wallmount enclosures can be used for virtually any application. The WM series ensures NEMA protection through a secure locking system, foamed-in-place gasket, and knife-edge sealing surface. Features include a stainless steel body and door, and a zinc plated mounting panel.

Features

Model No.	WM 8018.521
Material	Door: Stainless steel, all-round foamed-in PU seal Housing and door: Stainless steel 1.4301 (AISI 304) Mounting plate: Carbon steel, zinc-plated
Surface finish	Brushed
Supply includes	Housing with door(s) Door hinged on left Mounting plate Wall mounting blind-nuts
Dimensions	Width: 900 mm Height: 1,500 mm Depth: 400 mm
Dimensions of mounting plate (W x H)	840 mm x 1,455 mm
Protection category NEMA	NEMA 4X
Material thickness - door	2 mm
Material thickness - enclosure	2 mm
Material thickness – mounting plate	2.5 mm
Lock	Lock version: 3-point locking system
Packaging unit	1 pc(s).
Net weight	246.914

Features

Gross weight	247.5
Customs tariff number	7326908688
UPC-Code	83543

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity