

Rittal – The System.

Faster – better – everywhere.



WM 8018.633

WM wall-mounted disconnect enclosure

State: 2026-04-03 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



WM 8018.633 - WM wall-mounted disconnect enclosure 304 stainless steel

These flange mount disconnect wallmount enclosures can be used for virtually any application. The WM series ensures NEMA protection through a secure locking system, foamed-in-place gasket, and knife-edge sealing surface. Features include a stainless steel body and door, and a zinc plated mounting panel.



Features

Model No.	WM 8018.633
Material	Door: Stainless steel, all-round foamed-in PU seal Housing and door: Stainless steel 1.4301 (AISI 304) Mounting plate: Carbon steel, zinc-plated
Surface finish	Brushed
Supply includes	Housing with door Door hinged on left Wall mounting blind-nuts Flange door with universal disconnect cutout
Dimensions	Width: 825 mm Height: 900 mm Depth: 300 mm
Dimensions of mounting plate (W x H)	704 mm x 870 mm
Protection category NEMA	NEMA 4X
Material thickness - door	2 mm
Material thickness - enclosure	2 mm

Features

Material thickness – mounting plate	3 mm
Packaging unit	1 pc(s).
Net weight	41.887 lb
Gross weight	123.999 lb
Customs tariff number	7326909099

Approvals

Explanations	Declaration of conformity
--------------	---------------------------