

# Rittal – The System.

Faster – better – everywhere.



## WM 8018.692

## WM wall-mounted enclosure

State: 2026-04-05 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# WM 8018.692 - WM wall-mounted enclosure stainless steel, with Roof Slope

The WMS slope top wallmount enclosure is designed for any environment that requires frequent washdowns. The 20 degree overhanging sloped roof prevents water from accumulating on top of the enclosure and door opening.

## Features

Model No.	WM 8018.692
Material	Door: Stainless steel, all-round foamed-in PU seal Housing and door: Stainless steel 1.4301 (AISI 304) Mounting plate: Carbon steel, zinc-plated
Surface finish	Brushed
Supply includes	Housing with door Door hinged on left Mounting plate Wall mounting blind-nuts 20° overhanging slope top
Dimensions	Width: 300 mm Height: 395 mm Depth: 210 mm
Dimensions of mounting plate (W x H)	254 mm x 375 mm
Protection category NEMA	NEMA 4X
Material thickness - door	2 mm
Material thickness - enclosure	1.5 mm
Material thickness – mounting plate	1.5 mm
Lock	Lock version: Quarter turn
Packaging unit	1 pc(s).
Net weight	21.164 lb

# Features

---

Gross weight	21.199 lb
Customs tariff number	8538100000

---

# Approvals

---

Explanations	Declaration of conformity
--------------	---------------------------