

Rittal – The System.

Faster – better – everywhere.



WM 8018.702

WM wall-mounted enclosure

State: 2025-12-21 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



WM 8018.702 - WM wall-mounted enclosure stainless steel, with Roof Slope

The WMS slope top wallmount enclosure is designed for any environment that requires frequent washdowns. The 20 degree overhanging sloped roof prevents water from accumulating on top of the enclosure and door opening.

Features

Model No.	WM 8018.702
Material	Door: Stainless steel, all-round foamed-in PU seal Housing and door: Stainless steel 1.4301 (AISI 304) Mounting plate: Carbon steel, zinc-plated
Surface finish	Brushed
Supply includes	Housing with door Door hinged on left Mounting plate Wall mounting blind-nuts 20° overhanging slope top
Dimensions	Width: 600 mm Height: 755 mm Depth: 300 mm
Dimensions of mounting plate (W x H)	549 mm x 730 mm
Protection category NEMA	NEMA 4X
Material thickness - door	2 mm
Material thickness - enclosure	1.5 mm
Material thickness – mounting plate	2.5 mm
Lock	Lock version: Quarter turn
Packaging unit	1 pc(s).
Net weight	78.699

Features

Gross weight	79.365
Customs tariff number	7326908688
UPC-Code	84049

Approvals

Explanations	Declaration of conformity
--------------	---------------------------