

Rittal – The System.

Faster – better – everywhere.



TS 8018.807

TS 8 Floormount Enclosure

State: 2025-12-20 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8018.807 - TS 8 Floormount Enclosure

Rittal's Floormount TS 8 combines the strength of unibody floormount enclosures with the flexibility of Rittal's revolutionary modular design. With its double door configuration and wide range of accessories, Rittal's Floormount TS 8 is sure to meet your UL Type 12 needs.

Features

Model No.	TS 8018.807
Material	Enclosure frame: Carbon steel, 1.5 mm Roof: Carbon steel, 1.5 mm Door: Carbon steel, 2.0 mm Rear wall: carbon steel, 1.5 mm Mounting panel: Carbon steel, 3.0 mm
Surface finish	Enclosure frame: Dipcoat-primed Door, roof and rear panel: Dipcoat-primed, powder-coated on the outside, textured paint Mounting plate and base plates: Zinc-plated
Color	RAL 7035
Supply includes	Enclosure frame with door(s) Roof plate Rear panel, detachable 4 eyebolts Padlock Comfort handle Base Plates Mounting plate 12 inch removable floor stands
Dimensions	Width: 1,600 mm Height: 1,800 mm Depth: 600 mm
Packaging unit	1 pc(s).
Net weight	679.989
Gross weight	679.989
Customs tariff number	7326909099
UPC-Code	84373

Approvals

Approvals

UL + C-UL (listed)