

Rittal – The System.

Faster – better – everywhere.



TS 8026.548

Baying systems TS 8

State: 2026-06-11 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8026.548 - Baying systems TS 8 Type 3R

Rittal perfected the concept of the industrial modular enclosure with the TS 8 series. These single door, UL Type 3R rated enclosures consist of a frame with door, rear wall, and roof plate. Purchase sidewalls and plinth separately for complete assembly.

Features

| | |
|--------------------------|--|
| Model No. | TS 8026.548 |
| Material | Enclosure frame: Carbon steel, 1.5 mm Roof: Carbon steel, 1.5 mm Door: Carbon steel, 2.0 mm Rear wall: carbon steel, 1.5 mm Mounting panel: Carbon steel, 3.0 mm |
| Surface finish | Enclosure frame: powder-coated Door, roof and rear panel: Dipcoat-primed, powder-coated on the outside, textured paint Mounting plate and base plates: Zinc-plated |
| Color | RAL 7035 |
| Supply includes | Enclosure frame with door(s) Roof plate Rear panel, detachable 4 eyebolts Base Plates Mounting plate |
| Dimensions | Width: 1,000 mm Height: 2,200 mm Depth: 600 mm |
| Protection category NEMA | NEMA 3R |
| Packaging unit | 1 pc(s). |
| Net weight | 364.993 lb |
| Gross weight | 364.993 lb |
| Customs tariff number | 9403200082 |

Approvals

Approvals

UL + C-UL (listed)