Rittal – The System.

Faster – better – everywhere.



TS 8106.235 Side wall, screwable, carbon steel

State: 2025-12-10 (Source: rittal.com/ca-en)



ENCLOSURE

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

TS 8106.235 - Side wall, screwable, carbon steel for TS, TS IT

Side panels, screw-fastened, sheet steel, for TS.

Features

Model No.	TS 8106.235	
Benefits	Automatic potential equalization and higher EMC protection thanks to enclosure panel holders with grounding insert Easy positioning with the location aid Grounding bolt with contact surface	
Material	Carbon steel, 1.5 mm	
Surface finish	Dipcoat-primed, powder-coated on the outside	
Color	RAL 7035	
Supply includes	Assembly components	
Note	Enclosure panel holders may optionally be fitted from the inside or outside of the enclosure. Area available for population: External dimension – 100 mm	
Suitable for	Enclosure type: TS TS IT Height: 2,000 mm Depth: 600 mm	
Protection category IP to IEC 60 529	IP 55	
Base material	Carbon steel	
Packaging unit	2 pc(s).	
Net weight	28	
Gross weight	29.2	
Customs tariff number	94039910	
EAN	4028177205260	

© Rittal 2025

Features

E-Number Sweden	E7282533	
ETIM 9	EC002524	
ECLASS 8.0	27182101	

Approvals

Explanations Declaration of conformity UK

© Rittal 2025 3