


Rittal – The System.

Faster – better – everywhere.



VX 8106.245

Side wall, screwable, carbon steel

State: 2025-08-04 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8106.245 - Side wall, screwable, carbon steel for VX

Side panels, screw-fastened, sheet steel, for VX.

Features

Model No.	VX 8106.245
Benefits	Time-saving mounting through clip-on side panel holder Automatic potential equalization and higher EMC protection due to enclosure panel holders with internal grounding insert Easy positioning in height and depth with placement aid One-man installation Grounding stud with large, paint-free contact surface for optimal support
Material	Carbon steel, 1.5 mm
Surface finish	Dipcoat-primed, powder-coated on the outside
Color	RAL 7035
Supply includes	Assembly components
Suitable for	Enclosure type: VX Height: = 2,000 mm Depth: = 600 mm
Protection category IP to IEC 60529	IP 55 IP 66
Type rating according to UL 50E	Type 1 Type 3R Type 4 Type 12
Base material	Carbon steel
Packaging unit	2 pc(s).
Net weight	26
Gross weight	29
PCF/VE (cradle-to-gate)	110.5 kg CO2 eq (Cat B)

Features

Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	94039910
EAN	4028177827417
E-Number Sweden	E3465116
ETIM 9	EC002524
ECLASS 8.0	27182101

Approvals

Approvals	UL + C-UL (listed)
-----------	--------------------