


Rittal – The System.

Faster – better – everywhere.



VX 8122.245

Side wall, screwable, carbon steel

State: 2026-07-08 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8122.245 - Side wall, screwable, carbon steel for VX

Side panels, screw-fastened, sheet steel, for VX.

Features

| | |
|-------------------------------------|--|
| Model No. | VX 8122.245 |
| Benefits | Time-saving mounting through clip-on side panel holder Automatic potential equalization and higher EMC protection due to enclosure panel holders with internal grounding insert Easy positioning in height and depth with placement aid One-man installation Grounding stud with large, paint-free contact surface for optimal support |
| Material | Carbon steel, 1.5 mm |
| Surface finish | Dipcoat-primed, powder-coated on the outside |
| Color | RAL 7035 |
| Supply includes | Assembly components |
| Suitable for | Enclosure type: VX IT Height: = 2,200 mm Depth: = 1,200 mm |
| Protection category IP to IEC 60529 | IP 55 |
| Type rating according to UL 50E | Type 1 Type 12 |
| Base material | Carbon steel |
| Packaging unit | 2 pc(s). |
| Net weight | 74 kg |
| Gross weight | 76 kg |
| PCF/VE (cradle-to-gate) | 174.58 kg CO2 eq (Cat B) |
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |

Features

| | |
|-----------------------|--|
| Customs tariff number | 94039910 |
| ETIM 9 | EC002524 |
| ECLASS 8.0 | 27182101 |
| Product description | VX Side panel, screw-fastened, for HD: 2200x1200 mm, sheet steel |

Approvals

| | |
|--------------|--------------------|
| Approvals | UL + C-UL (listed) |
| Explanations | PCF-declaration |
