### Rittal – The System.

Faster – better – everywhere.





## TS 8126.235 Side wall, screwable, carbon steel

State: 2025-10-26 (Source: rittal.com/ca-en)



# TS 8126.235 - Side wall, screwable, carbon steel for TS, TS IT

Side panels, screw-fastened, sheet steel, for TS.

#### **Features**

Model No.	TS 8126.235	
Benefits	Automatic potential equalization and higher EMC protection thanks	
	to enclosure panel holders with grounding insert	
	Easy positioning with the location aid	
	Grounding bolt with contact surface	
Material	Carbon steel, 1.5 mm	
Surface finish	Dipcoat-primed, powder-coated on the outside	
Color	RAL 7035	
Supply includes	Assembly components	
Note	Enclosure panel holders may optionally be fitted from the inside or	
	outside of the enclosure.	
	Area available for population: External dimension – 100 mm	
Suitable for	Enclosure type: TS	
	TS IT	
	Height: 2,200 mm	
	Depth: 600 mm	
Protection category IP to IEC 60 529	IP 55	
Base material	Carbon steel	
Packaging unit	2 pc(s).	
Net weight	29	
Gross weight	32	
Customs tariff number	94039910	

© Rittal 2025

### **Features**

E-Number Sweden	E7282535	
ETIM 9	EC002524	
ECLASS 8.0	27182101	

© Rittal 2025 3