Rittal – The System.

Faster – better – everywhere.





TS 8128.235 Side wall, screwable, carbon steel

State: 2025-11-04 (Source: rittal.com/ca-en)



TS 8128.235 - Side wall, screwable, carbon steel for TS, TS IT

Side panels, screw-fastened, sheet steel, for TS.

Features

| Model No. | TS 8128.235 |
|--------------------------------------|---|
| Benefits | Automatic potential equalization and higher EMC protection thanks |
| | to enclosure panel holders with grounding insert |
| | Easy positioning with the location aid |
| | Grounding bolt with contact surface |
| Material | Carbon steel, 1.5 mm |
| Surface finish | Dipcoat-primed, powder-coated on the outside |
| Color | RAL 7035 |
| Supply includes | Assembly components |
| Note | Enclosure panel holders may optionally be fitted from the inside or |
| | outside of the enclosure. |
| | Area available for population: External dimension – 100 mm |
| Suitable for | Enclosure type: TS |
| | TS IT |
| | Height: 2,200 mm |
| | Depth: 800 mm |
| Protection category IP to IEC 60 529 | IP 55 |
| Base material | Carbon steel |
| Packaging unit | 2 pc(s). |
| Net weight | 43 |
| Gross weight | 44 |
| Customs tariff number | 94039910 |
| EAN | 4028177237223 |

© Rittal 2025

Features

| E-Number Sweden | E7238412 | |
|-----------------|----------|--|
| ETIM 9 | EC002524 | |
| ECLASS 8.0 | 27182101 | |

© Rittal 2025 3